

## IN 19 LK 10-140

### Screwdriver bit socket 1/2"

with ball end, for in-hex screws, long pattern

Code	ETIM
<b>6166800</b>	<b>EC002157</b>
EAN	UNSPSC
<b>4010886616680</b>	<b>27-11-17-01</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-04-02</b>
Customs tariff number	
<b>82079030</b>	



### Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- Total swivel angle approx. 15-20°

### Article information

Contents (Qty of pieces)	1	Standard	DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,153 kg	Width across flats l [mm]	10
Total length [mm]	140 mm	Backup	Ball Catching Cricket
Surface	chrome-plated	Tip length	102,0 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	22,5 mm
Drive connector square female [metric]	12,5 mm	Total swivel angle	15 - 20°
Drive connector square female [inch]	1/2"		