EM7078-000 ✔ ACTIVE

Raychem | P-Clamps

TE Internal #: EM7078-000

P-Clamps, Cable Mounting & Harness Accessories, P-Clamp, 3 Clamp Size, Cable Bundle Diameter .125 – .25 in [3.18 – 6.35 mm], AS21919 Size 3

View on TE.com >

Harnessing > Cable Mounting & Harness Accessories

Cable Mounting Accessory Type: **P-Clamp**

Clamp Size: **3**

Cable Bundle Diameter: **3.18 – 6.35 mm [.125 – .25 in]**

AS21919 Size: **3**

Features

Product Type Features

Cushion Material	Chloroprene
Clamp Material	PEEK
Cable Mounting Accessory Type	P-Clamp

Body Features

Weight per Piece	3.5 g

Dimensions

Cable Bundle Diameter	3.18 – 6.35 mm[.125 – .25 in]

Usage Conditions

Operating Temperature Range	-65 – 85 °C[-85 – 185 °F]

Industry Standards

AS21919 Size	3

Other

Clamp Size	3

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # EG3246-000
LWB-103-6.0(100)

TE Part # EG1595-000
CBMS-10-P



TE Part # 0697834002
NTFR-1/2-0-SP

TE Part # 216005-007
55A0111-20-9

Also in the Series | P-Clamps

Cable Mounting & Harness Accessories (10)

Customers Also Bought

TE Part #EM7080-000
THA-PDKG-07

TE Part #EM7087-000
THA-PDKG-21

TE Part #EM7079-000
THA-PDKG-05



TE Part #5-2176403-0
3550 110R 1%



TE Part #2176408-6
3560 680R 5%



TE Part #1051686-1
2031 5102 00

TE Part #YDTS20F11-35JNV001
D38999: Square Flange, 11-35 insert

TE Part #YDTS20F13-35JAV001
D38999: Square Flange, 13-35 insert

TE Part #YDTS20F15-35JAV001
D38999: Square Flange, 15-35 insert



TE Part #1616043-7
B-140AP-1=RELAY

Documents

Product Drawings

THA-PDKG-03

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_EM7078-000_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_EM7078-000_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_EM7078-000_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

TE Connectivity P-Clamp

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English