



mecalectro

Safety holding electromagnet – 5.11.05



Diameter: 17 mm

Holding force when power on: 3.5 daN

Power Consumption: 1.5 W

Total mass: 35 g

Degree of protection / Energetic class: UP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 12 to 48Vcc

Duty Cycle: Permanent (100%)

Standard: NF 61-937

Examples of applications: Maintenance of fire dampers or smoke evacuation traps, blocking of parts, positioning, control of ventilation flaps.