

Interface module - VIP-2/PT/FLK20/LED - 2904251

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 20-pos., with LED

The illustration shows a 14-position version



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 813624
Weight per Piece (excluding packing)	137.2 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	57.1 mm
Height	72.1 mm
Depth	56 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	24 V DC
Max. perm. current (per branch)	1 A
Number of positions	20
Status display	LED
Mounting position	any
Standards/regulations	IEC 60664

Interface module - VIP-2/PT/FLK20/LED - 2904251

Technical data

General

	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max.	14
Stripping length	8 mm

Connection data for connection 2

Connection name	Flat-ribbon cable connection
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	20

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421

Interface module - VIP-2/PT/FLK20/LED - 2904251

Classifications

UNSPSC

UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A
Nominal voltage UN	24 V


UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A

cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current IN	1 A

EAC

Interface module - VIP-2/PT/FLK20/LED - 2904251

Approvals

cULus Recognized  us

Accessories

Accessories

System cable

Cable - FLK 20/EZ-DR/ 50KONFEK - 2296391



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 0.5 m

Cable - FLK 20/EZ-DR/ 100KONFEK - 2296401



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 1.0 m

Cable - FLK 20/EZ-DR/ 150KONFEK - 2296472



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 1.5 m

Cable - FLK 20/EZ-DR/ 200KONFEK - 2296485



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 2.0 m

Interface module - VIP-2/PT/FLK20/LED - 2904251

Accessories

Cable - FLK 20/EZ-DR/ 300KONFEK - 2296498



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 3.0 m

Cable - FLK 20/EZ-DR/ 400KONFEK - 2296508



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 4.0 m

Cable - FLK 20/EZ-DR/ 600KONFEK - 2296511



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 6.0 m

Cable - FLK 20/EZ-DR/ 800KONFEK - 2296524



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 8.0 m

Cable - FLK 20/EZ-DR/1000KONFEK - 2296537



Round cable set, with 20-position socket strips, 1:1 connection, can be used, for example, for MODICON TSX Micro, Premium, Quantum, no. of positions: 20, cable length 10.0 m

Interface module - VIP-2/PT/FLK20/LED - 2904251

Accessories

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Drawings

Circuit diagram

