



Image may differ from product. See specification for details.

TLGH 1

Manual operated grease gun

The SKF Grease Gun TLGH 1 is ideal for usage in agricultural, industrial and construction industries and for private use. The grease gun is delivered with a 175 mm (6.9 n.) extension pipe and hydraulic gripping nozzle.

- Suitable for usage with cartridges and loose grease
- Knurled body for firm and safe grip
- High quality steel is dent-resistant for easy cartridge loading
- Special piston design for smooth emptying of cartridges
- Supplied with extension pipe and hydraulic gripping nozzle

Overview

Dimensions

Reservoir volume	500 ml
Filling connection	DIN 1283
Length	380 mm

Performance

Maximum pressure	40 MPa
Maximum pressure	400 bar
Volume per stroke	0.9 ml

Properties

Recommended applications	For manual filling of greasing points in industrial, construction and agricultural applications
Grease supply	Loose or Cartridge
Use of standard grease cartridges	Yes, type DIN 1284
NLGI class of lubricant (max)	2
Suitable for grease nipples	Standard nipples as per DIN 71412
Operation	Two hands
Pipe/Hose thread connection	M10x1
Extension pipe	Yes, 175 mm
Hose	Optional
Can be filled with Grease filler pump	Yes, with SKF LAGF 18 or LAGF 50

Logistics

Product net weight	1.26 kg
eClass code	23-06-91-06
UNSPSC code	15121902

Compatible products

Spare part

Spare nozzle for Manual operated grease gun	1077600-1 A
Spare filling nipple for Manual operated grease gun	1077600-3
Spare pressure hose for grease gun	1077601

Accessory

Grease nipple set	LAGN 120
Grease nozzle set	LAGS 8
Grease fitting caps and tags	TLAC 50/B
Grease fitting caps and tags	TLAC 50/G
Grease fitting caps and tags	TLAC 50/R
Grease fitting caps and tags	TLAC 50/Y
Grease fitting caps and tags	TLAC 50/Z

Recommended product

Grease meter, measuring grease discharge	LAGM 1000E
Ultrasound lubrication checker	TLGU 10
Grease filler pump for use on drums	LAGF 18
Grease filler pump for use on drums	LAGF 50
Manual operated grease gun	1077600
Manual operated grease gun	1077600 H
Manual operated grease gun set	1077600/SET
Manual operated grease gun, one handed	LAGH 400



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.