
quick exhaust valve SE-3/8-B Part number: 9687



Data sheet

Feature	Value
Valve function	Quick exhaust
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Mounting type	Threaded
Standard nominal flow rate, exhaust	2,760 l/min
Standard nominal flow rate for pressurisation 6->5 bar	2,880 l/min
Operating pressure	0.2 10 bar
Ambient temperature	-20 75 °C
Material housing	Aluminium die cast
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Nominal size	11 mm
Assembly position	Any
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Medium temperature	-20 75 °C
Product weight	125 g
Pneumatic connection, port 3	G3/8
Materials note	Conforms to RoHS
Material seals	NBR



FESTO