

Datasheet

Stock No: 9175103**RS Pro Oil Resistant Delivery Hose**

Internal Diameter	38.0mm
	1 1/2"
External Diameter	47.0mm
Wall Thickness	4.5mm
Maximum Working Pressure	8.0 Bar
Weight Per Meter	0.68 Kg
Bend Radius	171mm
Vacuum Mtrs H2O	9
Material	Flexible PVC
Working Temperature	-10°C to +55°C
Length	5 M