

# 7446 // SONIC STEP MID FIT

Boots  
PPE risk category II



Sporty design  
With dial fastener 711 // FIT SYSTEM  
Well padded bootleg for optimal fit and comfort



## 7446 // SONIC STEP MID FIT



|                        |   |
|------------------------|---|
| <b>Shoe upper:</b>     | Split leather, grey   Action Leather, black |
| <b>Outsole:</b>        | EVA / nitrile, black / white                |
| <b>Size(s):</b>        | 36-48                                       |
| <b>Packaging unit:</b> | 10 pair(s)                                  |
| <b>Certification:</b>  | EN ISO 20345, EN IEC 61340-4-3              |

NITRAS SONIC STEP MID FIT, safety boots, half-height, S3S FO HRO SC, durable split leather / Action Leather, grey / black, durable EVA / nitrile outsole, black / white (colour code: 1210), fibreglass toe cap, textile perforation resistant midsole, metal-free, premium COMFORT STEP insoles, ergonomically formed, sporty design, with dial fastener 712 // FIT SYSTEM for fast availability and optimal fit, highest slip resistance (SR), width 11, heel lining for easy donning and doffing and heel reinforcement made of robust microfibre, well padded bootleg for optimal fit and comfort, DGUV Rule 112-191-proofed, Type 1, ESD-capable, PPE risk category II

EN ISO 20345

EN IEC 61340-4-3



### Industries

-  Craft
-  Building / Construction
-  Landscape gardening
-  Waste management
-  Transport / Logistics

### Advantages

- + Sporty design
- + With dial fastener 711 // FIT SYSTEM
- + Well padded bootleg for optimal fit and comfort



Further images

---



**Additional information**

---

**Miscellaneous**

Weight (g) 610

**Logistics data**

---

| Size | GTIN (SPU)    | GTIN (PU)     | Length (m) | Width (m) | Height (m) | Weight (kg) | Quantity PU / pallet |
|------|---------------|---------------|------------|-----------|------------|-------------|----------------------|
| 36   | 4059904209886 | 4059904210011 | 0,645 m    | 0,545 m   | 0,34 m     | 13,3 kg     |                      |
| 37   | 4059904209893 | 4059904210028 | 0,645 m    | 0,545 m   | 0,34 m     | 13,5 kg     |                      |
| 38   | 4059904209909 | 4059904210035 | 0,645 m    | 0,545 m   | 0,34 m     | 13,7 kg     |                      |
| 39   | 4059904209916 | 4059904210042 | 0,645 m    | 0,545 m   | 0,34 m     | 13,9 kg     |                      |
| 40   | 4059904209923 | 4059904210059 | 0,645 m    | 0,545 m   | 0,34 m     | 14,1 kg     |                      |
| 41   | 4059904209930 | 4059904210066 | 0,645 m    | 0,545 m   | 0,34 m     | 14,3 kg     |                      |
| 42   | 4059904209947 | 4059904210073 | 0,645 m    | 0,545 m   | 0,34 m     | 14,5 kg     |                      |
| 43   | 4059904209954 | 4059904210080 | 0,67 m     | 0,595 m   | 0,37 m     | 14,7 kg     |                      |
| 44   | 4059904209961 | 4059904210097 | 0,67 m     | 0,595 m   | 0,37 m     | 14,9 kg     |                      |
| 45   | 4059904209978 | 4059904210103 | 0,67 m     | 0,595 m   | 0,37 m     | 15,1 kg     |                      |
| 46   | 4059904209985 | 4059904210110 | 0,67 m     | 0,595 m   | 0,37 m     | 15,3 kg     |                      |
| 47   | 4059904209992 | 4059904210127 | 0,67 m     | 0,595 m   | 0,37 m     | 15,5 kg     |                      |
| 48   | 4059904210004 | 4059904210134 | 0,67 m     | 0,595 m   | 0,37 m     | 15,7 kg     |                      |

Customs tariff number: 64034000000

Country of origin: China