

	SINAMICS S200 Basic, with PROFi Input voltage: 200-240 V 1/3 AC; -15%/+10%; 1.2/0.6A 50/60Hz; Output voltage: 0-inpu 0.8A; 0-550Hz; Motor: 0.1kW Degree of protection: IP20 FSA, 40x170x135 (WxHxD)
--	---

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)
<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com>

