



TECH POWER - FLEX S3

Réf. : 70804



Suitable for :	Inside/Outside
Type :	Low shoe
Activity :	Construction / Storage, Logistic, Transport / Electronic Industry, ESD
Upper :	Water resistant full supple leather and CORDURA® material
Lining :	ARTICO® black color, up to the toes, slipper feeling
Tongue :	Bellows tongue in ON STEAM® microfibre, lining ARTICO® and padded with 10mm thick foam
Ankle protection :	
Fastening :	Round polyester black laces with "Quick lock" system
Toe cap :	Ultralight and extra wide 200 joules, Composite LIGHT SYSTEM®
Midsole :	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole :	Thermoformed in active carbon dual density foam, antistatic, ESD and antibacterial FRESH TECH®
Sole :	PU 2D, TECH SOLE® ankle anti-twist system, oil resistant FO, antistatic, HI-CI
Sole pattern :	Multi-purpose cleated indoor/outdoor outsole, well-defined heel, cleated arch, SRC standard
Weight (Kg/pair) :	1.200
Colors :	Black upper and dark grey/light grey outsole
Sizes :	35-48 (2-13)
Standard :	EN ISO 20345:2011 SRC / EN 61340-4-3 / DGUV 112-191
CE certificate of conformity N° :	0075/020/161/04/18/0585 EXT 09/04/18
Special features :	Quick fastening system "Quick lock"
Special features 2 :	Reflective piping on the heel part
Special features 3 :	

SPECIAL FEATURES

 Integral 100% composite
(Air System + Light System + Flex System)

 Metal free, non magnetic

 Water absorption and
penetration resistance of upper (WRU)

 **CORDURA**

 **on steam**

 **ARTICO**

G GENERAL FEATURES

	Antistatic properties (A)	YES	YES
	Heel energy absorption (E)	YES	YES
	Abrasion resistance	YES	YES
	Crampon sole	YES	YES
	Heat-insulated sole (HI)	YES	YES
	Cold-insulated sole (CI)	YES	YES
	200 joule extra-wide toecap	YES	YES
	Hyper-ventilated lining	YES	YES
	Perforation-resistance 1100 N (P)	YES	YES