



Main

Range	PowerPact
Product or component type	Panelboard
Product name	PowerPacT 4
Device application	Distribution
Colour	Cream (RAL 9001)
Provided equipment	Removable bottom gland plate end cover

Complementary

[In] rated current	800 A
Number of ways	18 ways (3P) 54 ways (1P)
[Ue] rated operational voltage	415 V 50 Hz AC
Breaking capacity	50 KA AC 1 s
Enclosure material	Epoxy-polyester powder steel
Cable entry	Top entry at main
Device mounting	Wall mounted
Height	2210 Mm
Width	850 Mm
Depth	260 Mm

Environment

IP degree of protection	IP3x
Standards	BS EN 60439-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	50 Cm
Package 1 Width	223 Cm
Package 1 Length	89 Cm
Package 1 Weight	122 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------