

DATA SHEET

page 1/2


Form 247-040924

Description

Part Number	Description
G4PB4	G4 4-Channel I/O Module Rack

The G4PB4 I/O mounting rack compactly accommodates up to four G4 I/O modules in applications where only a few I/O points are needed. Insert and remove modules easily and quickly without disturbing field wiring. Modules are secured to the mounting rack with a threaded captive hold-down screw.

Barrier strips with screw terminals provide the field, control, and mounting rack power connections.



Features

- Requires minimum panel space
- Built-in fuse tester
- Spare fuse on board
- UL recognized, CSA certified, CE approved
- Uses a single 5, 15, or 24 VDC power supply fo control power


Specifications

Operating temperature:	0 to 70° C
Interface connector (field and control):	Screw-type barrier strip accommodates up to 10 AWG wire

DATA SHEET

Form 247-040924

Dimensions



Connections

