



Part Number : [190130026](#)
Product Description : InsulKrimp Fully Insulated
Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 22-18
AWG, Expanded Red Insulator, Mylar Tape
Series Number : 19013
Status : Active
Product Category : Quick Disconnects
Engineering Number : AA-2317T



Documents & Resources

Drawings

[190130026 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-008-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19013
Description	InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 22-18 AWG, Expanded Red Insulator, Mylar Tape
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	822350961455

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V AC
-------------------	---------

Physical

Barrel Type	Closed - Brazed
Color - Resin	Red
Flammability	94V-2
Gender	Female

Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.231/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.50mm max.
Wire Size (AWG)	18, 20, 22

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>198132010</u>
Mini-Mac Applicator	<u>638852300</u>
Hand Crimp Tool	<u>640016300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640056300</u>