

Accessories

PROTECTIV CAP, N, plug (male)

61_N-0-0-1/-3

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



General data	
Technology	Radio Frequency
Weight	0.0143 kg
Outer conductor material	Brass / SUCOPLATE (R) Plating
Body material	Brass / SUCOPLATE (R) Plating
Gasket material	VMQ (Silicone rubber)
Other body part	Brass / SUCOPLATE (R) Plating
Operation temperature	165 °C
Remarks	Length of chain = 115 mmm - material of chain: brass

Ordering Information Table	
Item number	Item description
22542452	61_N-0-0-1/-3_-E

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1812 / Date of publication: 26.08.2025 / uncontrolled copy