



- 3-piece styles available
- Precision honed bore on straight bore couplings
- Does not mar the shaft
- NYPATCH® Anti-vibration hardware
- Additional Step Bores available
- Bore tolerance: +.051mm - .000mm
- Opposing hardware on 2-piece styles

PART NO. STEEL	PART NO. STAINLESS STEEL	BORE (mm)	BORE (mm)	OD (mm)	LENGTH L (mm)	FORGED CLAMP SCREW
MSPX-6-6-F	MSPX-6-6-SS	6	6	18	30	M3X8
MSPX-8-7-F	MSPX-8-7-SS	8	7	24	35	M3X10
MSPX-8-8-F	MSPX-8-8-SS	8	8	24	35	M3X10
MSPX-9-9-F	MSPX-9-9-SS	9	9	24	35	M3X10
MSPX-10-9-F	MSPX-10-9-SS	10	9	29	45	M4X12
MSPX-10-10-F	MSPX-10-10-SS	10	10	29	45	M4X12
MSPX-12-9-F	MSPX-12-9-SS	12	9	29	45	M4X12
MSPX-12-12-F	MSPX-12-12-SS	12	12	29	45	M4X12
MSPX-14-12-F	MSPX-14-12-SS	14	12	34	50	M5X16
MSPX-14-14-F	MSPX-14-14-SS	14	14	34	50	M5X16
MSPX-15-14-F	MSPX-15-14-SS	15	14	34	50	M5X16
MSPX-15-15-F	MSPX-15-15-SS	15	15	34	50	M5X16
MSPX-16-16-F	MSPX-16-16-SS	16	16	34	50	M5X16
MSPX-20-19-F	MSPX-20-19-SS	20	19	42	65	M6X16
MSPX-20-20-F	MSPX-20-20-SS	20	20	42	65	M6X16
MSPX-25-24-F	MSPX-25-24-SS	25	24	45	75	M6X16
MSPX-25-25-F	MSPX-25-25-SS	25	25	45	75	M6X16
MSPX-30-28-F	MSPX-30-28-SS	30	28	53	83	M6X18
MSPX-30-30-F	MSPX-30-30-SS	30	30	53	83	M6X18
MSPX-35-35-F	MSPX-35-35-SS	35	35	67	95	M8X25
MSPX-40-40-F	MSPX-40-40-SS	40	40	77	108	M8X25
MSPX-50-50-F	MSPX-50-50-SS	50	50	85	124	M10X25