

USB VGA Console Extender over CAT5 UTP (500 ft)

StarTech ID: SV565UTPUGB



The SV565UTPUGB USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

Features

- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Cables Included for a ready out of the box setup
- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands
- Supports most combo keyboard and mouse sets (including Wireless)
- Supports auto-switching between host and remote users or dedicated control

Technical Specifications

Warranty	2 Years
Color	Black
Enclosure Type	Steel
Product Height	20 mm [0.8 in]
Product Length	75 mm [3 in]
Product Weight	299 g [10.6 oz]
Product Width	155 mm [6.1 in]
Audio	No
KVM Ports	2
Multi-Monitor	No
PC Interface	USB
PC Video Type	VGA
Rack-Mountable	No
IP Control	No
Max Transfer Distance	150 m (492 ft)
Supported Resolutions	1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Female
Other Interface(s)	1 - RJ-45 Female
OS Compatibility	OS independent; No software or drivers required
Note	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
Center Tip Polarity	Positive
Input Current	0.2 A
Input Voltage	100 ~ 240 AC
Output Current	0.6 A
Output Voltage	9 DC
Plug Type	M
Power Source	AC Adapter Included
Humidity	0~80% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)

Shipping (Package) Weight	1.7 kg [3.8 lb]
Included in Package	1 - Host Unit
Included in Package	1 - Remote Unit
Included in Package	2 - 6 ft 2-in-1 USB VGA KVM cables
Included in Package	2 - Packs Rubber Feet
Included in Package	1 - Power Adapter
Included in Package	1 - Manual

Certifications, Reports and Compatibility

