

PRODUCT-DETAILS

# TY524MR-0

## TYRAP-PK-100PCS-BLACK-N66



### General Information

Extended Product Type	TY524MR-0
Product ID	7TCG009450R0171
EAN	5414363065524
Catalog Description	TYRAP-PK-100PCS-BLACK-N66
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 139.7mm (5.5 Inches), Width of 3.56mm (0.14 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 135 Newtons (30 Pounds)

### Ordering

EAN	5414363065524
UPC	786210613901

### Dimensions

Product Net Width	0.14 in 3.56 mm
Product Net Depth / Length	5.5 in 139.7 mm

### Container Information

Package Level 1 Units	100 piece
-----------------------	-----------

Package Level 2 Units	10000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

## Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

## Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	TY-RAP FASTENING
Product Type	High Performance
Tensile Strength	40 lb 178 N
Thickness	0.04 in 1 mm

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY524MR-0
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY524MR-0

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

