

FEATURES

- Colour: black
- Flammability rating: UL94V-0
- Linear Power Supply
- Output connector: 2.1mm x 5.5mm x 12mm

RS PRO, 20W Plug In Power Supply 12V ac, 1.6A, 1 Output Linear Power Supply, Type C

RS Stock No.: 139-1774



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

From RS PRO, comes a high quality 20W linear plug-in power supply. This linear power adapter is an excellent plug in power solution as it is cost effective, highly reliable and designed for use in Europe. As part of our RS Pro line of power adapters, you are ensured a reliable & robust power solution.

General Specifications

Type	Linear Power Supply
Plug Type	Type C
Output Connector	2.1mm x 5.5mm x 12mm Centre Positive
Input Connector	EU Plug
Number Of Outputs	1
Medical Approved	No
Applications	Fans, Radios, Video, Toys, Aquariums, Desk lamps and LED lamps

Electrical Specifications

Output Voltage	12V ac
Input Voltage	230 V ac, 240 V ac
Output Current	1.6A
Power Rating	20W
Leakage Current	0.25mA max. @ 264VAC, 50Hz
MTBF	50,000 hours (25 C)

Mechanical Specifications

Cable Length	1.8m
Width	60mm
Length	89mm
Depth	51mm
Humidity	30% - 85% RH

Operation Environment Specifications

Maximum Temperature	40°C
Minimum Temperature	-20°C

Approvals**Compliance/Certifications**

IEC/EN61558, EN55022:2010+AC:2011(IT) ,
EN55024:2010 (IT&AV), IEC61000-4-2/ESD
,IEC61000-4-3, IEC61000-4-4/EFT, IEC61000-4-
5/SURGE, IEC61000-4-6/CS

