



CC 60
E1621606
CABLE CUTTER 1-HANDED WITH STRIPPING BLADE 0.2-70mm²

Product Properties:

Grip design	1-component
With impact protection	No
Suitable for steel wire braiding	No
Replaceable cutting head	No
Cutting jaws exchangeable	No
With strip function	Yes
Insulated	Yes
Suitable for solid cores	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Construction/operation	Mechanic one hand
Isolation protection 1000 V	No
With spring	No

Dimensions:

Max. cable cross section	70 mm ²
MOQ	1 .
Unit	pcs
Suitable for max. cable diameter	15 mm
Total length	244 mm

Approvals:

VDE tested	No
------------	----

Isolation protection 1000 V

No

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
PFAS	No PFAS
REACH	No SVHC (247 Subs. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000142 - Cable shears
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	1-hand
Search Description	CCTOOLS
Alternative SKU	CC60
E-no	E1621606

Logistic information:

Barcode	733117631066
Country of origin	JP
E-no	E1621606
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	CC 60
Taric code	82032000
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.