



ENGLISH

Datasheet

RS Pro LED 5000 STROBE

Stock No: 134-6747



Description

Due to the configuration with 120 high performance LEDs, the RS STROBE 5000 LED offers a powerful light intensity.

The large, homogeneous illumination surface delivers superb results even at difficult light conditions, making the RS STROBE 5000 LED suitable for a very wide range of measurement, observation and inspection functions. It is especially suitable for demanding applications, such as those in the printing industry.

Outstanding light intensity for web width up to 500mm.

Features

Low wear LED technology

Light intensity & image sharpness adjustable

Large area illumination 300 x 500 mm

For widths wider than 500mm, strobes can be connected in parallel.

Technical Short Data

Frequency range: 0 ... 120,000 FPM

Light intensity max.: 7,500 LUX @ 30 cm

Illumination area : 30 x 50 cm

Dimensions: 224 x 130 x 112 mm

Scope of delivery

Stroboscope RS STROBE 5000 LED

Operating instructions

1 DIN plug 5-pin for trigger input and/or power

Power supply

Optional accessories

Strobe controller (RS part number 1346754)

Tripod (RS part number 1346765)

Articulating mounting arm (RS part number 1346764)

Eco Strobe controller (RS part number 1346755)

Mounting Kit (RS part number 1346763)

Connection cable (RS part number 1346766)

Extension cable (RS part number 1346767)

Strobe din plug (RS part number 1346762)