

FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight exposure
- **High Tensile Strength:** Withstands up to 18 kg, ensuring secure bundling of cables
- **Wide Temperature Range:** Operates effectively between -40 °C and 85 °C, suitable for diverse conditions
- **Flame Retardant:** UL 94 V-2 rating provides added safety in case of fire
- **ISO 9001 Certified:** Ensures consistent quality and reliability
- **RoHS and REACH Compliant:** Meets environmental and safety standards

RS PRO Standard Cable Tie, 140 mm Length

RS Stock No: 642-843



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO standard cable ties are designed for securing and organising cables efficiently. Made from durable polyamide, they offer reliable performance in various environments. Ideal for both industrial and domestic applications, these cable ties ensure a neat and tidy setup.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Standard
Tensile Strength	18 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	140 mm
Material	Polyamide
Maximum Bundle Diameter	31 mm
Width	3.5 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	ISO 9001 SGS, REACH, RoHS, UL94V-2
---------------------	------------------------------------