

fine filter

MS6-LFM-1/2-BRM-DA

Part number: 536835

FESTO

1 µm filter, plastic bowl with plastic bowl guard, manual condensate drain, with differential pressure indicator, direction of flow from left to right.



Data sheet

Feature	Value
Series	MS
Size	6
Design structure	Fibre filter
Grade of filtration	1 µm
Condensate drain	manual rotary
Operating pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [5:7:3]
Max. standard flow rate for air quality class	950 l/min
Min. standard flow rate for air quality class	140 l/min
Filter efficiency	99.99 %
Max. condensate volume	38 cm ³
Bowl guard	Plastic guard
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Storage temperature	-10 ... 60 °C
Residual oil content	0.5 mg/m ³
Differential pressure display	Visual indicator
Mounting type	Optional Line installation with accessories
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Material housing	Aluminium die cast
Material filter	Boron silicate fibre
Material bowl	PC
Material seals	NBR
Materials note	Free of copper and PTFE Conforms to RoHS
Product weight	600 g