

# Bellows kit EADB-V2-40-S201-300

Part number: 2828836

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                                     |
|--------------------------------|-------------------------------------------|
| Outside diameter               | 57 mm                                     |
| Size                           | 40                                        |
| Stroke range                   | 201 mm ... 300 mm                         |
| Piston rod extension           | 90 mm                                     |
| Design                         | Round                                     |
| Mounting position              | optional                                  |
| Design                         | Bellows kit<br>With ducted exhaust air    |
| Corrosion resistance class CRC | 3 - high corrosion stress                 |
| LABS (PWIS) conformity         | VDMA24364-B2-L                            |
| Media resistance               | Dust<br>Chips<br>Oils<br>Grease<br>Petrol |
| Degree of protection           | IP65<br>To IEC 60529                      |
| Ambient temperature            | -10 °C ... 80 °C                          |
| Moving mass                    | 99 g                                      |
| Product weight                 | 164 g                                     |
| Type of mounting               | Push-on<br>Via threaded pin               |
| Pneumatic connection           | G1/4                                      |
| Note on materials              | RoHS-compliant                            |
| Material adapter components    | Wrought aluminium alloy<br>Anodised       |
| Material seals                 | NBR                                       |
| Material bellows               | NBR                                       |
| Material threaded pin          | High-alloy stainless steel                |