

STANLEY

FMHT70401-0

STANLEY® FATMAX® 4-in-1 Multi Tacker

The STANLEY® FATMAX® 4-in-1 Multi Tacker is a multi-functional stapler to tackle multiple professional fastening applications including securing alarm and telephone cables, fastening drywall and plasterboard, fencing, panelling and roof sheeting. It features an anti-jam mechanism for continuous, reliable operation, as well as a belt clip for convenience and easy transportation. Takes Type A, Type G, Type J and Type CT100 Staples and Brad Pins.



FEATURES & BENEFITS

EASY SQUEEZE TECHNOLOGY: For reduced fatigue and added driving power into materials.

ANTI-JAM MECHANISM: Prevents fasteners jamming, for continuous use and reliable operation.

STAPLER FOOT: Keeps stapler at correct angle for optimum pressure on the nose

STAPLE RELOAD: Easy to reload staple gun.

BELT CLIP: For convenient storage whilst working and easy transportation.

SOFT GRIP HANDLE: For added comfort.

COMPATIBLE FASTENINGS: Fires STANLEY® Type-A staples in 6mm - 14mm, STANLEY® Type-G staples in 6mm - 14mm, STANLEY® Crown CT100 in 10mm - 14mm and STANLEY® Type-J in 15mm.

STAPLES NOT INCLUDED.



STANLEY®

FEATURES & BENEFITS



SUITABLE FOR A VARIETY OF APPLICATIONS

Ideal for securing alarm and telephone cables, fastening drywall and plasterboard, fencing, panelling and roof sheeting, plus more.



STAPLER FOOT

Keeps stapler at correct angle for optimum pressure on the nose



STAPLE WINDOW: Provides clear visibility to determine when staple reload is required.



STAPLE RELOAD

Easy to reload staple gun.



BELT CLIP

For convenient storage whilst working and easy transportation.



COMPATIBLE FASTENINGS

Fires STANLEY® Type-A staples in 6mm - 14mm, STANLEY® Type-G staples in 6mm - 14mm, STANLEY® Crown CT100 in 10mm - 14mm and STANLEY® Type-J in 15mm.