

TY175-50X-100



CBL TIE 50LB 7IN UV BLACK NYL



General Information

Extended Product Type	TY175-50X-100
Product ID	7TAG054360R0179
EAN	5414363075165
Catalog Description	CBL TIE 50LB 7IN UV BLACK NYL
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 186.43mm (7.34 Inches), Width of 4.674mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), 100 Pack
Lock Type	Plastic Pawl

Ordering

EAN	5414363075165
Minimum Order Quantity	100 piece
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	1.701 g
--------------------	---------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	127 mm
Package Level 1 Height	31.75 mm
Package Level 1 Depth / Length	304.8 mm
Package Level 1 EAN	00075114952354
Package Level 2 Units	1000 piece
Package Level 2 Width	213.36 mm
Package Level 2 Height	160.02 mm
Package Level 2 Depth / Length	248.92 mm
Package Level 2 EAN	50075114952359

Additional Information

Brand / Label	Ty-Fast
---------------	---------

Color	Black
Material	Nylon/Polyamide 6.6
Product Main Type	CABLE TIES AND ACCESSORIES
Product Name	PLASTIC CABLE TIE
Product Type	Cable Tie
Standards	UL E49405
UPC	075114952354

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY175-50X-100
Instructions and Manuals	TY175-50X-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

