



**Low Profile
T&B Catalog Number:**

SF100-18-100

UPC Number:

78621019171

Status:

Active

Description:

Cable Tie 18lb 4" White All-Nylon Low-Profile

Features

Low-Profile, contoured head reduces clearance required for the bundle and enhances the appearance of your harness.

The safeguard wall eliminates exposure to sharp edges.

The saddleback fits snug against the contour of the wiring harness.

General

Material Nylon 6.6

Color Natural

Dimension Information

Nominal Length (inches) 4

Length (inches) 4.65

Width (inches) .095

Max. Wire Bundle Diameter (inches) 1

Min. Wire Bundle Diameter (inches) .125

Thickness (inches) .043

Specifications

Temperature Rating -40°F to 185°F

Flammability Rating UL 94 V-2

Packaging

T&B Order Multiple 100

T&B Inner Pack 100

Package in Units 1000

Package Type Regular

T&B Sold in UOM Each

T&B Weight Per UOM 6.25 lbs. per 100

Application Support

Overview Available on Website

Material Selection Guide Available on Website

Certifications

RoHS Compliance Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com