

MB4A0C2

Article Number: 151-28403

Adhesive Bases, .18" Max tie width, 1.12" Length/Width, .18" Hole Dia., PA66, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number MB4A0C2

Type MB4A

Color Black (BK)

- Features and Benefits**
- For use with 18 and 30 pound cable ties to provide stability when securing bundles.
 - Secures with rubber based adhesive backing and/or two or four screws.
 - 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.

Product Description HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

Fixation Method (FF) Screw Mounting and Adhesive

Short Description Adhesive Bases, .18" Max tie width, 1.12" Length/Width, .18" Hole Dia., PA66, Black, 100/pkg

Product Dimensions

Length L (imperial) 1.12 "

Length L (metric) 28.5 mm

Width W (imperial) 1.12 "

Width W (metric) 28.5 mm

Cable Tie Width Max (imperial) 0.18 "

Cable Tie Width max. (metric) 4.6 mm

Height H (imperial) 0.22 "

Height H (metric) 5.6 mm

Mounting Hole Diameter D (imperial) 0.18 "

Mounting Hole Diameter D (metric) 4.6 mm

Mounting Hole Centers (imperial) 0.8 "

Mounting Hole Centers (metric) 20.2 mm

Logistics and Packaging

Quantity per bag

Package Quantity 100

Carton Quantity 4000

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Shortcut Adhesive	Synthetic rubber
Adhesive	Rubber
CSA Certified	No
Flammability	UL94 V2 (excluding adhesive)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Conformity	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes