

TV Wall Mount supports up to 100 inch VESA Displays - Low Profile Full Motion TV Wall Mount for Large Displays - Heavy Duty Adjustable Tilt/Swivel Articulating Arm Bracket

Product ID: FPWARTS2



This swivel tv wall mount is ideal for a meeting space, lobby, boardroom, classroom or other venues. It provides an impressive and secure way to display a flat-panel TV or mount a digital signage display, while saving valuable space.

Robust Steel Construction

Engineered from high-grade steel, the heavy duty tv wall mount securely supports VESA compatible displays, including curved TVs, up to 100" with a weight capacity of 165 lb. (75 kg).

Full-Motion Adjustment

With a smooth and effortless motion, you can extend the articulating arm out from the wall up to 31.7" (805 mm). You can also retract the arm back to nest just 2.9" (75 mm) away from the wall.

Find the Right Viewing Angle

Swivel your screen +/- 60 degrees and tilt your screen -2 to +15 degrees for ideal viewing and to reduce glare. The TV wall mount bracket also has a screen level adjustment, so you can adjust your display up to 3 degrees clockwise or counterclockwise after it is installed.

The Choice of IT Pros Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

FPWARTS2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep guests informed in hotels, restaurants and other venues
- Securely wall-mount your TV for easy viewing in boardrooms, lobbies, classrooms and meeting spaces
- Save space by wall-mounting your TV in your home theater

Features

- **LARGE 100" TV WALL MOUNT:** This heavy-duty TV wall mount supports VESA compatible displays incl. curved TVs up to 100 inch (165 lb/75 kg) w/ a durable full-motion steel frame and a powder-coated finish
- **WIDE RANGE OF MOTION:** Articulating TV wall mount offers +/-90° swivel, +2/-15° tilt & +/-3° LCD screen level adjustment & arms allow low-profile at 2.9" (75 mm) from wall or extend to 31.7" (805 mm)
- **LATERAL ADJUSTMENT:** Full motion TV wall mount w/ post-install lateral shifting lets you center the display on a wall or corner, w/ 16"/24" off-centered studs w/ range of 47"/1.2m from left to right
- **COMPATIBILITY:** Universal TV wall mount supports LG, Samsung, Sony, Sharp, among others (screws/spacers incl) & VESA hole patterns 200x100, 200x200, 300x200, 300x300, 400x200, 400x200, 400x400, 600x400
- **TIDY AESTHETIC:** The adjustable tv wall mounting bracket w/ integrated cable management & optional black snap-on covers keeps flat screen cables organized; ideal for customer-facing digital signage

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Minimum Profile from Wall	2.8 in [70 mm]
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	200x100 mm
		200x200 mm
		300x200 mm
		300x300 mm
		400x200 mm
400x300 mm		
400x400 mm		
600x400 mm		
Wallmountable	Yes	
Performance	Display Swivel	+90° / - 90°
	Display Tilt	+2° / -15°
	Fits Curved Display	Yes
	Maximum Arm Extension	25.6 in [650 mm]
	Maximum Display Size	100"
	Minimum Arm Extension	2.8 in [70 mm]
	Minimum Display Size	37"
	Screen Level Adjustment	+3° / -3°
	Swivel / Pivot	+90° / -90°
	Weight Capacity (Per Display)	165.8 lb [75 kg]
Physical Characteristics	Product Height	487.000
	Product Length	26.4 in [67 cm]
	Product Width	800.000
	Weight of Product	16800.000
Packaging Information	Package Height	3.9 in [10 cm]

	Package Length	21.7 in [55 cm]
	Package Width	36.4 in [92.5 cm]
	Shipping (Package) Weight	41.7 lb [18.9 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - TV Wall Mount Assembly 1 - Wall Mounting Bracket 2 - TV Mounting Brackets 2 - Decorative Covers 2 - Mounting Plates 7 - M6 x 15 screws 7 - Round Washers, Small 1 - Wrench 1 - Hex Key 4 - M5 x 14 Screws 4 - M6 x 14 Screws 4 - M6 x 30 Screws 4 - M8 x 30 Screws 4 - M8 x 50 Screws 4 - Rectangular Washers 8 - Small Spacers 8 - Large Spacers 6 - Mounting Screws 6 - Wall Anchors 6 - Round Washers, Large 1 - User Manual

Product appearance and specifications are subject to change without notice.