



Main

Range	Odace
Product or component type	Wireless repeater
Device application	Repeater
Device mounting	Flush
Device presentation	Mechanism with fixing frame and central plate
Colour tint	Anthracite

Complementary

Communication port protocol	IEEE 802.11 b/g/n
Transmission rate	300 Mbps (MCS15, 40 MHz)
Network security encrypting	WPA2-PSK
Actuator	Push-button
Switch application	On/off switching
[Ue] rated operational voltage	100...240 V
Control type	ON/OFF button
Integrated connection type	Wi-Fi
Fixing mode	Clip-on support
Height	45 mm
Width	45 mm
Depth	39 mm
Net weight	0.53 kg
Market segment	Residential
Targeted channel	Professional
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP20
Standards	IEEE 802.11 b/g/n
Ambient air temperature for operation	-20...40 °C
Ambient air temperature for storage	-30...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information