

- ✓ **5" (12cm) cone-type speaker**
- ✓ **Easy installation thanks to TOA's original SUS spring-based installation method**
- ✓ **Finely crafted design in white that harmonize with the venue's architecture and decor**

Integrated with speaker unit and panel, the PC-1869S Ceiling Mount Speaker is of all metallic construction and is ideal for Public address announcements and BGM. Featuring the V-shaped spring catch mechanism for easy installation. The input impedance can easily be changed by changing the tap position of the transformer. The push-in type terminal block makes cable connection easy and allows bridge wiring.

Specification

Rated Input	6W (100V line) / 3W (70V line)
Rated Impedance	100V line; 1.7k ohms (6W), 3.3k ohms (3W), 6.7k ohms (1.5W), 13k ohms (0.8W) 70V line; 1.7k ohms (3W), 3.3k ohms (1.5W), 6.7k ohms (0.8W), 13k ohms (0.4W)
Frequency Response	55 - 18,000Hz
Speaker Component	5" (12cm) cone-type
Input Terminal	Push-in terminal
Sound Pressure Level	90 dB
Dimensions	ø180 × 72 (D) mm (ø7.09 × 2.83")
Finish	Baffle: Steel Plate, white Grille: Surface-treated steel plate net, white

