



## PRODUCT-DETAILS

**SPL20/25M****20MM GS-PVC COAT CONDUIT 25M - BL****General Information**

<b>Extended Product Type:</b>	SPL20/25M
<b>Product ID:</b>	7TCA296030R0140
<b>EAN:</b>	5020963000126
<b>Catalog Description:</b>	20MM GS-PVC COAT CONDUIT 25M - BL
<b>Long Description:</b>	Liquid Tight, Oil Resistant, Medium Flexibility Conduit, 1/2 Inch, Nominal Conduit Size 20mm, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 25 Meters, PVC Covering with Galvanised Steel Core, Black
<b>Display Name:</b>	SPL20/25M

**Additional Information**

<b>Product Main Type:</b>	Adaptaflex Flexible Cable Protection
<b>Application:</b>	Liquid Tight - Indoors / Outdoors, Marine, Buildings

**Ordering**

<b>EAN:</b>	5020963000126
-------------	---------------

UPC: 786210246888

---

## Dimensions

---

Outside Diameter: 21.1 mm

---

---

## Technical

---

Number of Batteries: 0

Color: Black

Material: Galvanized Steel Core with PVC Covering

---

---

## Environmental

---

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

---

## Container Information

---

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963000126

Package Level 1 Height: 8 in  
203 mm

Package Level 1 Depth / Length: 16 in  
406 mm

Package Level 1 Width: 16 in  
406 mm

---

---

## Certificates and Declarations

---

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

---

---

## External Classifications and Standards

---

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

---

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

