

**1498/SP150**

**Conventional battery charger / starter, 12 V**

CE

Safety and reliability in any situation thanks to high-quality electronics.

Features:

- For lead-acid storage batteries
- Charging current selector
- Ammeter
- Thermostatic long start protector
- Short-circuit protection fuse
- Reverse polarity protector

6,6 Kg

Technical data:

- Power supply (1ph): 230 V - 50/60 Hz
- Power: 190 W
- Voltage: 12 V
- Maximum current: 15 A
- Charging current: 11 A
- Max. boost current: 120 Acc
- Starting current: 85 A
- Charging capacity: 165 Ah 15h
- Charging positions: 2 + boost



|  | art.       | L<br>mm | P<br>mm | H<br>mm |
|---------------------------------------------------------------------------------|------------|---------|---------|---------|
| 014980745                                                                       | 1498/SP150 | 260     | 200     | 175     |