

rotronic

Datenblatt - Fiche technique - Data sheet

11.02.8977




ROLINE USB 3.0 Kabel, Typ A-A, ST/BU, 0,8m

ROLINE Câble USB 3.0 Type A-A, M/F, 0,8 m


ROLINE USB 3.0 Cable, Type A M – A F, 0.8 m

ROHS-COMPLIANT


USB 3.0 A/M 9PIN
INS:BLUE(PT 300C)



L ± T



USB 3.0 A/F 9PIN
INS:BLUE(PT 300C)



NOTE:

- CABLE: UL-2725 [#28(7/0.127 T.C)×1P INS:Foam-PE+D.W(7/0.127 T.C)
+AL/MY+Hot-melt-Mylar]×2C+#28(7/0.127 T.C)×1P INS:Polyolefin
+#28(7/0.127 T.C)×2C INS:Polyolefin+AL/MY+B.D.(85%)
PVC JACKET; OD:5.2±0.15mm COLOR:BLACK(NK-K01) REV 3.0.
- CONNECTOR:
P1: USB 3.0 A TYPE MALE 9PIN CONTACT:30U",SHELL:NI-PLATED.
P2: USB 3.0 A TYPE FEMALE 9PIN CONTACT:30U",SHELL:NI-PLATED.
- HOOD:MOLDED TYPE,PVC 45P, COLOR:BLACK(NK-K01).
- ELECTRICAL TEST:
(1)100% OPEN SHORT & MIS WIRE TEST.
(2)CONTACT RESISTANCE 3 ohm Max.
(3)INSULATION RESISTANCE 10M ohm Min.
△ 5 PACKING:<1>EACH PC / ROLINE SMALL HEADER CARD
<2>EACH PC / ROLINE BIG HEADER CARD
50 PCS / CARTON

PIN OUT	P1	P2	CABLE FUNCTION
1	RED	1	PWR
2	WHITE	2	UTP_D-
3	GREEN	3	UTP_D+
4	BLACK	4	GND_PWRrt
5	BLUE	5	SDP1-
6	YELLOW	6	SDP1+
7	D.W	7	SDP1_Drain & SDP2_Drain
8	PURPLE	8	SDP2-
9	ORANGE	9	SDP2+
	SHELL		SHELL

DWG	P/N	L(mm)	T(mm)	PACKING
170-3781-3	11.02.8977	800	10	<1>
170-3781-2		3000	30	<2>
170-3781-1	11.02.8978	1800	30	<1>

Tolerance Inch M/M		Title	
X	.015 .30	USB 3.0 A/M - A/F CABLE	
XX	.010 .10		
XXX	.005 .05		
Draw	FANNIE 05/03/10'	Customer P/N	
Check		App'd	Customer: T-RAG
Engr		Scale	NONE
		Units	M/M
		Dwg No.	170-3781
		REF:	II
		Sheet:	1/1

Rotronic co., LTD.

LTR	REV.	DESCRIPTION	DATE
△*4	II	EDIT PACKING ADD LENGTH/P/N	05/03/10'