

Gripper finger cap
HAMA-GA-B33-40-2-S-40-BU
Part number: 8203480

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Min. ø to be gripped	30 mm
Max. ø to be gripped	55 mm
Working stroke	0 mm ... 55 mm
Number of gripper fingers	2
Design	For grippers
Design	Form-fitting Frictional locking
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C ... 60 °C
Product weight	68 g
Colour	Blue
Shore hardness	A 40 +5
Note on materials	RoHS compliant
Gripper finger material	VMQ (silicone), metal detectable