



**KW 3000**

DATASHEET

# CHERRY KW 3000

The CHERRY KW 3000 wireless keyboard comes in the popular full-size layout, which includes arrow keys and a number pad. The keyboard can be installed quickly and easily using plug and play — simply plug the supplied nano USB receiver into the USB port. The wireless 2.4-GHz technology ensures that the connection is almost entirely free from interference and provides a range of up to 10 meters.

The keyboard has a simple and clear layout: In addition to the F1–F12 keys, there are four hotkeys for quick access to calculator, email and browser functions as well as sleep mode. The CHERRY KEYS software can be used to assign your preferred functions to any additional keys and is available to download free of charge. The battery status indicator can be seen at a glance, being located directly above the Fn keys.

The keys enable fast, precise and silent typing whilst being extremely durable. With an impressive service life of up to 10 million keystrokes, the CHERRY KW 3000 is a reliable computer accessory for long-term use.

GS approval ensures maximum safety. The non-slip underside of the keyboard ensures that it remains securely in place at your workstation, even when the two feet are folded out and the keyboard is used in an elevated position.

In summary, the wireless CHERRY KW 3000 keyboard offers a variety of features that make it a very reliable accessory: Easy to install, user-friendly and durable.



## HIGHLIGHTS

- Full-size layout incl. arrow keys and number pad
- Flat, wireless keyboard
- Low-noise keys with durable key labels
- Up to 10 million keystrokes
- Four hotkeys for calculator, email, browser and sleep mode
- Plug-and-play installation via USB port (nano USB receiver)
- Almost interference-free wireless 2.4 GHz technology (range of up to 10 meters)
- Battery status indicator
- Stable, fold-out feet for height adjustment
- Non-slip bottom
- Free CHERRY KEYS software for assigning your preferred function to certain keys
- GS approval for certified safety

## SCOPE OF DELIVERY

- Manual
- Keyboard
- Nano-USB-Receiver
- 1 x AAA battery

# TECHNICAL DATA

## PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A

## TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching

Palm rest	Palm rest not available
USB-Hub	no
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
---------------------	---

Battery type	Alkaline
Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

# PRODUCT VARIANTS

<b>PART NUMBER</b>	<b>LAYOUT</b>	<b>COLOUR</b>
JK-3000	CN (China)	black
JK-3000DE-2	DE (Germany)	black
JK-3000ES-2	ES (Spain)	black
JK-3000EU-2	EU (USA+ €-Symbol)	black
JK-3000FR-2	FR (France)	black
JK-3000GB-2	GB (United Kingdom)	black
JK-3000PO-2	PO (Portugal)	black

## CHERRY KW 3000 [JK-3000]



**Layout:** CN (China)  
**Product colour:** Black

---

Part number	JK-3000
-------------	---------

---

### PRODUCT INFORMATION

---

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A

---

### TEMPERATURE

---

Min. operating temperature	0 °C
Max. operating temperature	50 °C

---

### KEYBOARD

---

Keycap material	ABS
Key labeling	Laser etching

---

Palm rest	Palm rest not available
USB-Hub	no
Number of keys	105 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

### **WIRELESS**

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

### **BATTERY**

Number of batteries	1
Battery type	Alkaline
Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes

Battery charging socket no

---

## KW 3000 [JK-3000DE-2]



**Layout:** DE (Germany)

**Product colour:** Black

Part number	JK-3000DE-2
EAN	4025112109812

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	473 mm × 205 mm × 26 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Number of keys	105 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline

Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## KW 3000 [JK-3000ES-2]



**Layout:** ES (Spain)  
**Product colour:** Black

Part number	JK-3000ES-2
EAN	4025112109850

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	473 mm × 205 mm × 26 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Number of keys	105 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline

Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## KW 3000 [JK-3000EU-2]



**Layout:** EU (USA+ €-Symbol)

**Product colour:** Black

Part number	JK-3000EU-2
EAN	4025112109836
UPC	840183609177

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	473 mm × 205 mm × 26 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Number of keys	104 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline

Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## KW 3000 [JK-3000FR-2]



**Layout:** FR (France)  
**Product colour:** Black

Part number	JK-3000FR-2
EAN	4025112109829

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	473 mm × 205 mm × 26 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Number of keys	105 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline

Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## KW 3000 [JK-3000GB-2]



**Layout:** GB (United Kingdom)

**Product colour:** Black

Part number	JK-3000GB-2
EAN	4025112109843

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	473 mm × 205 mm × 26 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Number of keys	105 + 4
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline

Battery design	AAA
Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## KW 3000 [JK-3000PO-2]



**Layout:** PO (Portugal)

**Product colour:** Black

Part number	JK-3000PO-2
EAN	4025112119224

### PRODUCT INFORMATION

Model number	JG-07
Reliability	MTBF > 45.000 Stunden
Warranty	1 additional year voluntary limited manufacturers warranty
Product approvals	<ul style="list-style-type: none"><li>- CE</li><li>- China RoHS</li><li>- FCC</li><li>- GS</li><li>- UKCA</li><li>- cULus</li><li>- RCM</li><li>- Windows Hardware Compatibility</li></ul>
Software support	CHERRY KEYS
Operating system	<ul style="list-style-type: none"><li>- Windows 7</li><li>- Windows 8</li><li>- Windows 10</li><li>- Windows 11</li></ul>
System Requirements-Hardware	USB-A
Dimensions inc. packaging	477 mm × 206 mm × 30 mm   702 g

### TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	50 °C

## KEYBOARD

Keycap material	ABS
Key labeling	Laser etching
Palm rest	Palm rest not available
USB-Hub	no
Illumination	no
Adjustable feet	integrated
Status LEDs	in housing
Key technology	Rubberdome
Service life per key (in million strokes)	10 mio. actuations
Max. current consumption (mA) of keyboard	3 mA
Keyboard format	Full-size (100%)
Integrated metal plate	no
Volume (dB) of keyboard	40 db
N-Key Rollover	no
Anti-ghosting	no
Key encryption	no
Internal memory	no
Windows key	with Windows key

## WIRELESS

USB dongle	yes
2.4 Ghz wireless connection	yes
Wireless range	10 m
Encryption in wireless mode	no

## BATTERY

Number of batteries	1
Battery type	Alkaline
Battery design	AAA

Battery rechargeable	no
Battery replaceable	yes
Battery charging socket	no

## © Cherry Europe GmbH

Cherrystraße 2 · 91275 Auerbach/OPf. · Germany  
**cherry-world.com · cherry.de**

Sales Support · Technischer Support · eHealth Support

**+49 9643 - 2061 - 100**  
**www.cherry.de/de-de/kontakt**

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed. Actual battery life is strongly depending on individual user behavior and hardware setup.