

EchoMax XPS-30 Ultrasonic level transducer: continuous, non-contact, 30 m (98.42 ft) for liquids and solids. Mounting thread and facing: 1 1/2" universal thread Cable length: 5 m (16.40 ft) Flange: Without mounting flange Approvals: ATEX II 1D, 2G Ex mb IIC T4 Gb, ATEX II 1D, 2G Ex tb IIIC T135°C Da, Ta = -40°C to +95°C; UKEX II 1D, 2G Ex mb IIC T4 Gb, UKEX II 1D, 2G Ex tb IIIC T135°C Da, Ta = -40°C to +95°C; IECEx SIR 13.0009X Ex mb IIC T4 Gb, IECEx SIR 13.0009X Ex tb IIIC T135°C Da, Ta = -40°C to +95°C Instruction Manual: Multi-Language Quick Start

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)
<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com>

