

Han-Fast Lock 10mm² m.Pin, Ag

Part number	09 08 000 7124
Specification	Han-Fast Lock 10mm ² m.Pin, Ag
HARTING eCatalogue	https://b2b.harting.com/09080007124

Identification

Category	Contacts
Series	Han-Fast [®] Lock
Type of contact	PCB contact
Description of the contact	With pin

Version

Pack contents	Single contact

Technical characteristics

Conductor cross-section	10 mm²
Operating current	≤60 A
Contact resistance	≤2 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (locking)	Copper alloy
Surface (locking)	Passivated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
OL / CSA	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	100
Net weight	2.26 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector