

Hard Polyurethane - TUH

TUH0428B-20

Datasheet

General series information

- Applicable tubing O.D.: Ø 4 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- Colours: black, white, blue and translucent.

Standard specifications

Size	0428 (O.D. Ø4, I.D. Ø2.8)
Color	B (Black)
Roll Length	20 m Roll
-	Air
Maximum operating pressure	0.8 MPa
Weight	0.250 Kg

Additional information

Catalogue

[T_EU.pdf](#)