

Wire bridge - FBSW 2-5/60MM - 3030170

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Wire bridge, length: 60 mm, width: 5.1 mm, number of positions: 1, color: red/black



Your advantages

- ✓ Flexible potential distribution, thanks to custom wire lengths
- ✓ Bridge terminal blocks of varying terminal widths with ease
- ✓ Easy, tool-free operation, thanks to plug-in contacts



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 055626 364643
GTIN	4055626364643
Weight per Piece (excluding packing)	2.980 g
Custom tariff number	85444290
Country of origin	Poland

Technical data

Technical data

Color	red/black
Material	CuSn
Number of positions	1
Length	60 mm
Height	4.7 mm
Width	5.1 mm
Flammability rating according to UL 94	V0
Maximum load current	10 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)

Wire bridge - FBSW 2-5/60MM - 3030170

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121421
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410