



## R-536

Hard-knuckle flame-resistant tactical gloves, featuring a leather palm and PVC palm patch



Impact Heat and Flame Resistance



Light Duty

## Hard-knuckle flame-resistant tactical gloves, featuring a leather palm and PVC palm patch

- **Specialized protection:** RINGERS® R536 tactical gloves' goatskin leather palm - with PVC palm patch and leather fingertip reinforcement - enhances durability and fit, while lightweight Nomex® material offers top-of-hand flame resistance
- **Unhindered usability:** A touchscreen-compatible middle fingertip design ensures safe, sustained productivity
- **Added defenses:** These safety gloves feature a PVC knuckle protector laminated with Kevlar®-blended fabric and low-profile TPR (thermoplastic rubber) for thumb and finger-area impact protection
- **Enhanced features:** Their index finger design enhances trigger feel, while a cuff closure with a hook and loop TPR pull tab makes for a secure fit and a cuff loop facilitates vest, belt and uniform hook attachment



### Industries

- Law Enforcement
- Emergency Medical Services



# R-536

Hard-knuckle flame-resistant tactical gloves, featuring a leather palm and PVC palm patch

### Key Features

- **Premium goatskin leather palm:** Improved durability and a contoured fit
- **Lightweight Nomex® material:** Flame resistance for the top of the hands
- **Touchscreen-compatible middle fingertip:** For safe, uninterrupted wear

### Performance Standards & Regulatory Compliance



2111XP

### Specifications

| BRAND   STYLE | DESCRIPTION         | Gauge | SIZE             | COATING COLOR | PACKAGE                     |
|---------------|---------------------|-------|------------------|---------------|-----------------------------|
| RINGERS® R536 | Cuff Style: Velcro® |       | 8, 9, 10, 11, 12 | Black         | 5 pairs/bag, 10 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd Internationaal, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Latin America & Caribbean Region**

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

**North America Region**

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

**Canada**

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

**Australia**

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

**Asia Pacific Region**

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

