
32687 DPZ-16-25-P-A Twin cylinder - Series: All



32687 DPZ-16-25-P-A Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383822	DPZ - 16-P-A Set of wearing parts	Spare parts: 3, 5, 7, 9, 10, 15	1	PC
1	343441	DPZ- 16- P-A Grooved nut	Tightening torque 5 Nm / 3.7 lbf ft Use locking compound 8181256 CYBERBOND TM44	2	PC
2	343425	DPZ- 16- P-A End plate		1	PC
3		DPZ-10/16-... Buffer	Not available separately, see position A	1	PC
4	200625	DIN 472-17X1 Retaining ring		4	PC
5	386132	WIFC4-8X14,2X5,2-TPE-U Wiper seal	Lubricate with 684474 LUB-KC1 during assembly	2	PC
6	347292	ARA-08-S0062,0-BHS Piston rod	Use locking compound 8181256 CYBERBOND TM44 Tightening torque 5 Nm / 3.7 lbf ft	2	PC
7		B-14X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
8	354369	DPZ- 16- P-A Bearing		2	PC
9		DSN- 16 Cushioning ring	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	2	PC
10		LEFC2-16X10X2,55-TPE-U Lip seal	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
11	760704	DSNU- 16- PA ET Piston magnet		2	PC
12	219924	ISO 4017-M5X16-8.8 Hexagon head screw	Tightening torque 5 Nm / 3.7 lbf ft	1	PC
13	200600	DIN 439-B-M5-04 Hex nut		1	PC
14			Not available	1	PC
15		DSN- 16 Cushioning ring	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	2	PC
16	343433	DPZ-16 End cap		2	PC