

MV72 - Modaflame Multi Norm Arc Softshell Jacket

Collection: Modaflame™ Softshell HV

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Softshell HV: 100% Polyester, laminated to TPU FR membrane, bonded with 60% Modacrylic, 39% Cotton, 1% Carbon Fibre

Outer Carton: 14



Product information

The Modaflame Multi Norm Arc Softshell Jacket is constructed from a highly protective 3 layer softshell fabric. Using modacrylic and carbon fibre elements, this softshell provides flame, chemical, anti-static and high visibility protection. An interactive zipper allows this softshell to be zipped into an outer jacket for additional insulation if required.

Modaflame™ Softshell HV

Modaflame™ Softshell HV is constructed as per Modaflame™ Softshell. Modaflame™ Softshell HV (Yellow) is additionally certified to EN ISO 20471. Modaflame™ Softshell HV (Orange) is additionally certified to EN ISO 20471 and RIS 3279.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1 B1 C2)

EN ISO 11611 Class 2 (A1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-2 APC 2

IEC 61482-2 IEC 61482-1-1 (ELIM 11 CAL/CM², ATPV 16 CAL/CM²)

EN 13034 Type PB [6]

EN ISO 20471 Class 3

RIS 3279 TOM Issue 2 (Orange Only)

Features

- Inherent flame resistant qualities will not diminish with washing
- Protects against radiant and convective heat
- Zipped pockets
- Drawcord adjustable hem
- Storm flap front to protect against the elements
- Hook and loop cuffs for a secure fit
- Chin guard for added comfort and stability
- Contrast colouring for added style
- Flame resistant zip
- Anti-static
- Interactive zip for added functionality

MV72 - Modaflame Multi Norm Arc Softshell Jacket

Commodity Code: 6101309000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/15186-02/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/16138-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
MV72ONRS	Orange/Navy	65.0	45.0	45.0	1.2000	0.1316	5036108330669	25036108819465
MV72ONRM	Orange/Navy	65.0	45.0	45.0	1.2200	0.1316	5036108330652	25036108819458
MV72ONRL	Orange/Navy	65.0	45.0	45.0	1.2700	0.1316	5036108330645	25036108819441
MV72ONRXL	Orange/Navy	65.0	45.0	45.0	1.3300	0.1316	5036108330676	25036108819472
MV72ONRXXL	Orange/Navy	65.0	45.0	45.0	1.3800	0.1316	5036108330683	25036108819489
MV72ONRXXXL	Orange/Navy	65.0	45.0	45.0	1.4160	0.1316	5036108349845	25036108838503
MV72ONR4XL	Orange/Navy	65.0	45.0	45.0	1.4700	0.1316	5036108349852	25036108838510