

## BHP451RFE

Max. in masonry	16 mm
Battery Type	Lithium-ion
Blows per minute	3: 0-25500 2: 0-9000 1: 0-4500 bpm
Vibration drilling	2.5 m/sec <sup>2</sup>
Battery quantity (3.0 Ah)	2
Vibration hammer drilling	10 m/sec <sup>2</sup>
No load speed	3. 0 - 1700, 2. 0 - 600, 1. 0 - 300 rpm
Max in steel	13 mm
Vibration K factor	2.5 m/sec <sup>2</sup>
Noise sound power	97 dB(A)
Noise sound pressure	86 dB(A)
Noise K factor	3 dB(A)
Max in wood	65 mm



**STANDARD EQUIPMENT:** 194204-5 18V Li-ion battery, 784206-5 DOUBLE ENDED BITS 45-150MM, 784207-3 DOUBLE ENDED BITS 45- 150MM, 784210-4 DOUBLE ENDED BITS 45- 150MM, 798308-1 DOUBLE ENDED BITS 45- 150MM

- High operation efficiency with high torque.
- Three speed gear box.
- Twin LED job light with afterglow.
- Keyless heavy duty metal chuck.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- 4 pole motor.
- Conveniently located push button for forward and reverse.
- High comfort grips.
- Metal gear box.