



ENGLISH

Datasheet

PUR 5m Long transparent Flexible Ducting Reinforced, 13mm Bend Radius , Applications Various

RS Stock number 4139118



Features

Description: A zinc plated spiral helix trapped between two layers of crystal polyurethane.
A lightweight ducting which has excellent internal and external abrasion resistance.

Temperature: -40° C to +120° C (max. 125° C for short periods)

Application: Ideally suited for the transfer of large granular abrasive particles such as sawdust, foundry, general industrial and agricultural applications

Advantages: Crystal clear, very flexible