



6-557315-3 | MP-88U-R-1
Modular Plug, 8P/8C, Unshielded, Round, 100 pcs

Body Features

Conductor Type Solid | Stranded

Configuration Features

Number of Positions 8
Keyed No

Contact Features

Contact Base Material Phosphor bronze
Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness 50.00 μin | 1.27 μm
Number of Contacts Loaded 8

Dimensions

Cable Jacket Outside Diameter Range 0.20 in | 5.1 mm
Conductor Outside Diameter 0.034–0.039 in | 0.86–0.99 mm
Conductor Wire Size 26–24 AWG

Housing Features

Housing Material Glass filled polycarbonate

Industry Standards

UL Flammability Rating UL 1863

Packaging Features

Packaging Quantity 100

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Cable Type Round, unshielded
Performance Category Category 5
Connector Style Plug
Jack Type RJ45

6-557315-3 | MP-88UR-1

Latch Style	Standard
Product Type	Connector
Shielded	No

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------