


FEATURES

- **Constant Voltage Operation:** Delivers a stable 12V output for consistent LED performance
- **Input Voltage Range:** Operates efficiently between 180 to 240 V AC, accommodating various power supplies
- **Dimming Compatibility:** Supports Leading Edge, PWM, and Trailing Edge dimming for flexible lighting control
- **IP20 Rating:** Suitable for indoor use, providing basic protection against dust
- **Single Output Design:** Simplifies installation and reduces wiring complexity
- **1.25 A Driver Current:** Ensures optimal power delivery to connected LEDs
- **Maximum Output Power of 15W:** Supports a range of LED lighting applications

RS PRO 15W Constant Voltage LED Driver, 12V Output

RS Stock No: 642-797



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED Driver is designed to provide a reliable power source for LED lighting systems. With a constant voltage output of 12V, it ensures stable performance for your lighting applications. Ideal for both residential and commercial settings, this driver supports efficient energy use and long-lasting operation.

General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	1.25 A
Input Voltage	180-240 V ac
Input Voltage Type	AC
Maximum Output Power	15 W
Output Voltage	12 V

Protection Category

IP Rating	IP20
-----------	------

Approvals

Standards/Approvals	CE, EN61347-1
---------------------	---------------