

# BK-3HCDE CASE

eneloop pro AA — Case Pack



## Key Specifications

| Parameter              | Value                                               |
|------------------------|-----------------------------------------------------|
| Part Number            | BK-3HCDE CASE                                       |
| Cell size              | AA (Mignon)                                         |
| Chemistry              | Ni-MH, LSD, high-capacity 'pro' line                |
| Nominal voltage        | 1.2 V                                               |
| Capacity (typ. / min.) | 2550 mAh / 2450 mAh                                 |
| Rechargeable cycles    | Up to 500 times                                     |
| Charge retention       | 70% after 5 years storage                           |
| Dimensions (H x Ø)     | ≈50.5 mm x 14.5 mm                                  |
| Weight                 | ≈31 g per cell                                      |
| Operating temperature  | -20°C to 50°C (discharge)                           |
| Pack type              | Bulk/case carton — multiple retail 4-packs per case |