

Zarges Multi-Purpose Ladder



Versatile and compact - for an array of tasks

- Easy to store and transport with four folding sections.
- Can be used as a lean-to ladder with / without 4th section as stand-off
- As a stepladder it can be ascended from both sides
- Manufactured from high strength aluminium extrusion
- High-strength connection between rung and stile.
- External width of ladder body: 350 mm
- Optional platform and handrail available for 42383 & 42381
- Standard: EN 131, 150 kilo rating

Product Code	Number of Rungs	Dimensions Folded (mm)	Height as Stepladder (m)	Height as Workplatform (m)	Extended Length (m)	Stile Dimension (mm)	Weight (kg)
42383 RS7990641	4 x 3	745x1000x275	1.75	0.99	3.62	58 x 25	12.5

Accessories

Product Code	Description
40926 RS: 7990644	Non-slip aluminium platform to suit 42383



7990641 fitted with 7990644 (Purchased as separate items)