



Part Number : [747641301](#)
Product Description : QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length
Series Number : 74764
Status : Active
Product Category : High-Speed I/O Cable Assemblies




Documents & Resources

Drawings

[747641301_sd.pdf](#)
[PK-74764-1301-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

| | |
|------------------------|---|
| Status | Active |
| Category | High-Speed I/O Cable Assemblies |
| Series | 74764 |
| Description | QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length |
| Assembly Configuration | Dual Ended Connectors |
| Comments | Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths. |
| Connector to Connector | QSFP+-to-4 SFP+ |
| Product Name | QSFP Plus,QSFP+,SFP Plus,SFP+ |
| Type | Pluggable |
| UPC | 884982451568 |

Electrical

| | |
|-----------|-----------|
| Data Rate | 10.0 Gbps |
| Impedance | 100Ω |

Physical

| | |
|-------------------|-----------------------|
| Cable Bundling | None |
| Cable Length | 3.0m |
| Circuits (Loaded) | TWO DIFFERENTIAL PAIR |
| Gender | Male-Male |

| | |
|---------------------|-----------|
| Lock to Mating Part | Yes |
| Net Weight | 483.500/g |
| Packaging Type | Bag |
| Release Style | Pull Tab |
| Single Ended | No |
| Wire/Cable Type | Twinax |
| Wire Size (AWG) | 30 |