



### Main

Range of product	Linery
Product or component type	Cable end
Cable end size	Medium
Standards	DIN 46228-1
Type of packing	Individual bag
Quantity per set	Set of 100
Cable cross section	16 mm <sup>2</sup>

### Complementary

Cable end type	Single conductor
Additional information	Non-insulated
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 6
Bezel size	Ø 7.5 mm
Tube diameter	5.8 mm
Length	18 mm
Tube length	18 mm

### Environment

Ambient air temperature for operation	-20...105 °C
---------------------------------------	--------------

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0607 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---